



APPLICATION - SALT

MATERIAL CHARACTERISTICS

Mined or solar salts are crushed to a wide range of particle sizes for uses such as road deicing, water softener salt and mixing salt for animal feed. Recrystallized edible salts are separated into various sizes for end products such as pretzel salt, table salt and flour salt. The bulk density of salt ranges from 70 to 80 pounds per cubic foot.

USER LIST (partial)

AKZO Salt
AM Salt
Canadian Salt LTD.
Cargill Salt
Diamond Crystal Salt
Domtar
Ecuadoriana de Sal
Moab Salt Company
Morton Salt
Quimica Del Pacifico
Sal Fibras Pilco S.A.
Sherkat Tolidi Ghaza

APPLICATION DATA

Mined salt is initially scalped at approximately 1/2". Road salt must be relatively free of fines to prevent caking, so -30 mesh material is removed by screening. Fines removal is also performed on water softener salts. Mixing salt is typically specified in range of -14/+40 mesh.

Edible salts normally have tighter specifications on their particle size distributions. Two common products are pretzel salt and table salt. Pretzel salt is produced by removing oversize at 14 mesh and removing fines at about 20 mesh. Table salt is finer, usually -40/+70 mesh. Flour salt has the finest particle size, typically -70 mesh.

ROTEX FEATURES

- Corrosion resistant design
- Ball mesh cleaning
- Totally enclosed - positive sealing
- 316 or 316L stainless steel contact parts
- Cable suspension option
- Low maintenance

ROTEX design features provide reliable, high efficiency performance

ROTEX[®] SCREENERS

ROTEX Screeners are self-contained production screening machines for separating dry materials according to particle size. Through their unique gyratory motion of the near-horizontal screen surface, combined with a positive screen mesh cleaning system, ROTEX provides unusually high efficiency and capacity - all the result of continuing development for hundreds of applications throughout scores of industries.

ROTEX Screeners are made in over 100 standard models, ranging from 1 to 5 screen surfaces, for separations with openings from 1/2" to 325 mesh. They are available in Automatic-Tensioning all-metal and sanitary models, and General-Purpose models for applications not requiring all-metal construction.

ROTEX FLOW OF MATERIALS ... FAST, EFFICIENT, ACCURATE

Material enters at top where it is distributed over the entire width of the screen surface and conveyed toward the discharge end. Larger particles remain above the screen surface, while smaller particles pass through. Model shown (above right) is a typical two-surface ROTEX, which separates material into three different grades. Other ROTEX models have one to five screen surfaces, producing two to six separate grades.

TWO SEPARATE SCREENING ACTIONS


1. Gyratory Motion rapidly distributes ... stratifies ... separates.

The unique gyratory motion of the near-level screen box distributes material rapidly over the screen surfaces with practically no vertical vibration or hop. Finer particles are quickly stratified and readily pass through the screen as larger particles are gently conveyed to the discharge end.



2. Bouncing Balls control screen blinding

The bouncing action of balls confined in beveled pockets beneath each screen surface dislodges particles by direct contact. These resilient balls also keep the screen surface alive, providing agitation to aid particle stratification and to separate particles that may tend to stick together.



"QUICK-SNAP" PROVIDES AUTOMATIC SCREEN TENSIONING AND QUICK, EASY SCREEN REMOVAL

Quick-Snap is the patented design on all Automatic-Tensioning models for attaching screen clothing to the screen frame by spring tension clips. By maintaining a uniform tension across the entire screen surface, the system ensures superior screening accuracy, reduced screen blinding and increased screen life. The tension clip design also permits quick removal and replacement of screen clothing, which greatly reduces downtime.



SMOOTH COUNTERBALANCED DRIVE

The ROTEX counterbalanced drive produces a vibration-free screening motion that is never self-destructive - so smooth that ROTEX may be cable-suspended without loss of screening performance.

VARIETY OF DESIGN OPTIONS

- Sanitary designs
- Special inlets and outlets
- Manual or pneumatic top cover clamps for positive seal
- Two-deck independently fed surfaces
- High temperature modifications
- Abrasion-resistant linings
- Floor mounting or cable suspension
- And many other options to suit the application

MATERIAL TESTING SERVICE

Rotex takes the guesswork out of selecting the proper screening equipment by maintaining a fully-equipped materials testing laboratory. Here your materials are analyzed and tests conducted under simulated production conditions, to help determine the appropriate machine size, optimum screen openings and machine settings for a given application. To make use of this free testing service, first obtain a lab sample control number by contacting the ROTEX Test Lab Supervisor.

CALL ROTEX FOR ASSISTANCE ON YOUR APPLICATION

ROTEX has specialized in process screening equipment for more than 80 years, leading the way with innovations that have become the standard of the industry. For assistance with your specific application, call your ROTEX Representative or Application Engineers in our Cincinnati office.

ROTEX INC.

1230 Knowlton Street
Cincinnati, Ohio 45223-1845 U.S.A.
Telephone 513-541-1236
Fax 513-541-4888

ROTEX INC.